RELEASED: REVISED:

8-24-89 5-13-10

637172
CONVERSION KIT
BACKUP WASHERS

637170 (REV. C) PTFE DIAPHRAGM SERVICE KIT

FOR 1-1/2" & 2" METALLIC DIAPHRAGM PUMPS (REPLACES 637124-44)

Both kits are required for the first time conversion only.

INSTALLATION NOTES

- The new PTFE Diaphragm profile direction will appear OPPOSITE of the diaphragm being replaced.
- Both diaphragms are clearly marked with "FLUID SIDE" and "AIR SIDE" orientation.
- The old 6-1/4" o.d. washers CANNOT be used with the new two-piece diaphragms.
- After the conversion only the 637170 Service Kit is required for normal scheduled maintenance or repair.
- When replacing diaphragm rod "O" rings in "-C" models use only one of the seven included. (Mfd after 5/88).



OLD STYLE


92757-4

PTFE BALL

Y220-230

2-3/4" O.D.

637170 PTFE SERVICE KIT



NOTE: RADIUS IS INSTALLED TOWARDS DIAPHRAGM

NEWSTYLE

* If screw is not stainless steel order Y5-107-T separately.

PN 97999-126



